EYP-RWE-0840-06515-1500-SOT02-0000

Revision 1.10

GAIN CHIPS AR coated Fabry-Perot Laser

General Product Information		
Product	Application	
widely tunable 840 nm modified Fabry-Perot Laser	Spectroscopy	
for use in an External Cavity Diode Laser (ECDL)	covering wavelengths	
sealed SOT Housing	between 790 and 870 nm	
Monitor Diode		

Absolute Maximum Ratings

Parameter	Symbol	Unit	min	typ	max
Storage Temperature	Ts	°C	-40		85
Operational Temperature at Case	T _C	°C	-20		50
Forward Current	I _F	mA			200
Reverse Voltage	V _R	V			0
Output Power (extracavity)	P _{opt}	mW			100

Recommended Operational Conditions

Parameter	Symbol	Unit	min	typ	max
Operational Temperature at Case	T _C	°C	15		40
Forward Current	I _F	mA			180
Output Power (extracavity)	P _{opt}	mW			80

Characteristics at 25° C at Begin Of Life

Parameter	Symbol	Unit	min	typ	max
Center Wavelength	λ _c	nm		840	
Tuning Range	$\Delta\lambda_{tun}$	nm	790		870
Output Power (extracavity)	P _{opt}	mW		50	
Cavity Length	L	μm		1500	
Reflectivity at Front Facet	R _{ff}			3 [.] 10 ⁻⁴	1·10 ⁻³
Polarization				TE	
Spatial Mode (transversal) TEM ₀₀					
Spectral Mode (longitudinal)			Sir	igle/Multi M	ode
Divergence parallel (FWHM)	$\Theta_{ }$	0		10	
Divergence perpendicular (FWHM)	Θ_{\perp}	o		23	

Measurement Conditions / Comments

Stress in excess of one of the Absolute Maximum Ratings can cause permanent damage to the device. Please note that a damaging optical power level may occur although the maximum current is not reached.

Measurement Conditions / Comments

Measurement Conditions / Comments

Tuning range and output power are estimated from the gain profile of the laser. The actual achieved wavelength and power are strongly influenced by the external cavity. Therefore eagleyard Photonics will give no guarantee on these parameters.

E field parallel to Pin 2 - Pin 3 - plane	
Fundamental Mode	
depending on operating conditions	
parallel to Pin 2 - Pin 3 plane (see p. 3)	
perpendicular to Pin 2 - Pin 3 plane (see p. 3)	

12489 Berlin GERMANY

fon +49. 30. 6392 4520 fax +49. 30. 6392 4529 info@eagleyard.com www.eagleyard.com





24.01.2018

EYP-RWE-0840-06515-1500-SOT02-0000

Revision 1.10

Monitor Diode

GAIN CHIPS AR coated Fabry-Perot Laser

Parameter	Symbol	Unit	min	typ	max
Monitor Detector Responsivity ($U_{R MD} = 5 V$)	I _{mon} / P _{opt}	µA / mW		20	

Package Dimensions


Parameter	Symbol	Unit	min	typ	max
Height of Emission Plane	d _{EP}	mm	3.50	3.65	3.70
Excentricity of Emission Center	R	mm			0.12
Pin Length	I _{PIN}	mm		14	

Package Pinout


- 1 Laser Diode Cathode, Monitor Diode Cathode, Case
- 2 Photo Diode Anode
- 3 Laser Diode Anode




M-type



Package Drawings





24.01.2018

Measurement Conditions / Comments
depends on the intracavity power of the ECDL setup

Measurement Conditions / Comments reference plane: top side of TO header reference: center of outer diameter of header

fon +49. 30. 6392 4520 fax +49. 30. 6392 4529 illed copy when printed. info@eagleyard.com www.eagleyard.com







EYP-RWE-0840-06515-1500-SOT02-0000

Revision 1.10


GAIN CHIPS AR coated Fabry-Perot Laser

Typical Measurement Results ex cavity





Unpacking, Installation and Laser Safety



Unpacking the laser diodes should only be done at electrostatic safe workstations (EPA). Though protection against electro static discharge (ESD) is implemented in the laser package, charges may occur at surfaces. Please store this product in its original package at a dry, clean place until final use. During device installation, ESD protection has to be maintained.

The RWE diode type is known to be sensitive against thermal stress. It should not be operated without appropriate optical feedback from an external cavity. Operating at moderate temperatures on proper heat sinks will contribute to a long lifetime of the diode.

The laser emission from this diode is close to the invisible infrared region of the electromagnetic spectrum. Avoid direct and/or indirect exposure to the free running beam. Collimating the free running beam with optics as common in optical instruments will increase threat to the human eye.

Each laser diode will come with an individual test protocol verifying the parameters given in this document.

Performance figures, data and any illustrative material provided in this specification are typical and must be specifically confirmed in writing by eagleyard Photonics before they become applicable to any particular order or contract. In accordance with the eagleyard Photonics policy of continuous improvement specifications may change without notice.



© All rights reserved by eagleyard Photonics GmbH. This data sheet will be electronically administered and is subject to change without notice. Uncontrolled copy when printed.

Rudower Chaussee 29 12489 Berlin GERMANY

eagleyard Photonics GmbH

fon +49. 30. 6392 4520 fax +49. 30. 6392 4529 copy when printed. info@eagleyard.com www.eagleyard.com





24.01.2018

eaglevard

