Revision 1.00

# **TOPTICA** eagleyard

2017-11-22

# TAPERED AMPLIFIERS Semiconductor Optical Amplifier

General Product Information	
Product	Application
960 nm Tapered Amplifier	Spectroscopy
C-Mount Package	



### Absolute Maximum Ratings

Parameter	Symbol	Unit	min	typ	max
Storage Temperature (non condensing)	Ts	°C	-40		85
Operational Temperature at Case (non cond.)	T <sub>C</sub>	°C	0		50
Forward Current	I <sub>F</sub>	А			3.5
Reverse Voltage	V <sub>R</sub>	V			2
Output Power	P <sub>opt</sub>	W			2.2

### Measurement Conditions / Comments

Stress in excess of one of the Absolute Maximum Ratings may damage the laser. Please note that a damaging optical power level may occur although the maximum current is not reached. These are stress ratings only, and functional operation at these or any other conditions beyond those indicated under Recommended Operational Conditions is not implied.

### **Recommended Operational Conditions**

	Unit	min	typ	max
Tc	°C	5		40
I <sub>F</sub>	А			3.2
P <sub>input</sub>	mW	10		50
P <sub>opt</sub>	W			2.0
	I <sub>F</sub> P <sub>input</sub>	I <sub>F</sub> A P <sub>input</sub> mW	I <sub>F</sub> A P <sub>input</sub> mW 10	I <sub>F</sub> A P <sub>input</sub> mW 10

### Characteristics at $T_{LD}$ = 25 °C at BOL

Parameter	Symbol	Unit	min	typ	max
Design Wavelength	λ <sub>c</sub>	nm		960	
Gain Width (FWHM)	Δλ	nm		20	
Temperature Coefficient of Wavelength	dλ / dT	nm / K		0.3	
Operational Current $@ P_{opt} = 2.0 W$	I <sub>op Gain</sub>	А			3.2
Output Power	P <sub>opt</sub>	W	2.0		
Amplification	G	dB			
Cavity length	L <sub>C</sub>	μm		4000	

Measurement Conditions / Comments
non condensing
with proper injection from a seed laser

### Measurement Conditions / Comments

with proper injection from a seed laser
with proper injection from a seed laser at recommende

© All rights reserved by eagleyard Photonics GmbH. This data sheet will be electronically administered and is subject to change without notice. Uncontrolled copy when printed.

eagleyard Photonics GmbH

Rudower Chaussee 29 12489 Berlin GERMANY fon +49. 30. 6392 4520 fax +49. 30. 6392 4529

info@toptica-eagleyard.com www.toptica-eagleyard.com


Revision 1.00

# TAPERED AMPLIFIERS Semiconductor Optical Amplifier

Characteristics at T <sub>LD</sub> = 25 °C	at BOL				cont'd
Parameter	Symbol	Unit	min	typ	max
Reflectivity at Front Facet	R <sub>ff</sub>			3.10-4	1.10-3
Reflectivity at Rear Facet	R <sub>rf</sub>			3.10-4	1.10-3
Input Aperture (at rear side)	d <sub>in</sub>	μm		3	
Output Aperture (at front side)	d <sub>out</sub>	μm		210	
Astigmatism	А	μm		670	
Input Divergence parallel (1/e <sup>2</sup> )	$\Theta_{\text{in}}     $	0		24	
Input Divergence perpendicular (1/e <sup>2</sup> )	$\Theta_{\text{in}\perp}$	0		37	
Output Divergence parallel (1/e <sup>2</sup> )	$\Theta_{\text{out}}     $	0		18	
Output Divergence perpendicular (1/e <sup>2</sup> )	$\Theta_{\text{out}\perp}$	0		37	
Polarization				TE	

# Measurement Conditions / Comments estimated at recommended maximum forward current E field parallel to junction plane

### Typical Measurement Results



Ordering Information:

Performance figures, data and any illustrative material provided in this specification are typical and must be specifically confirmed in writing by eagleyard Photonics before they become applicable to any particular order or contract. In accordance with the eagleyard Photonics policy of continuous improvement specifications may change without notice.



### © All rights reserved by eagleyard Photonics GmbH. This data sheet will be electronically administered and is subject to change without notice. Uncontrolled copy when printed.

eagleyard Photonics GmbH

Rudower Chaussee 29 12489 Berlin GERMANY fon +49. 30. 6392 4520 fax +49. 30. 6392 4529

info@toptica-eagleyard.com www.toptica-eagleyard.com





Revision 1.00

# TAPERED AMPLIFIERS Semiconductor Optical Amplifier

Package Dimensions					
Parameter	Symbol	Unit	min	typ	max
Height of Emission Plane	h	mm	7.05	7.10	7.20
C-Mount Thickness	t	mm		4.05	


### Package Pinout


Mounting Wire Housing

Cathode (-) Anode (+)

# (-) (+) heat spreader

### Package Drawings





Measurement Conditions / Comments

2017-11-22

ΙΟΡΤΙCΑ

eagleyard



© All rights reserved by eagleyard Photonics GmbH. This data sheet will be electronically administered and is subject to change without notice. Uncontrolled copy when printed.

eagleyard Photonics GmbH

Rudower Chaussee 29 12489 Berlin GERMANY fon +49. 30. 6392 4520 fax +49. 30. 6392 4529

info@toptica-eagleyard.com www.toptica-eagleyard.com

Revision 1.00

## **TAPERED AMPLIFIERS** Semiconductor Optical Amplifier

### Unpacking, Installation and Laser Safety

Unpacking the laser diodes should only be done at electrostatic safe workstations (EPA). Though protection against electro static discharge (ESD) is implemented in the laser package, charges may occur at surfaces. Please store this product in its original package at a dry, clean place until final use. During device installation, ESD protection has to be maintained.

The TPA diode type is known to be sensitive against thermal stress. It should not be operated without appropriate injection from a seed laser. Operating at moderate temperatures on proper heat sinks will contribute to a long lifetime of the diode. The chip should be protected against moisture. A water vapor content below 5000 ppm is recommended for applications with high reliability requirements.

The laser emission from this diode is close to the invisible infrared region of the electromagnetic spectrum. Avoid direct and/or indirect exposure to the free running beam. Collimating the free running beam with optics as common in optical instruments will increase threat to the human eye.

Each laser diode will come with an individual test protocol verifying the parameters given in this document.



© All rights reserved by eagleyard Photonics GmbH. This data sheet will be electronically administered and is subject to change without notice. Uncontrolled copy when printed.

eagleyard Photonics GmbH

Rudower Chaussee 29 12489 Berlin GERMANY fon +49. 30. 6392 4520 fax +49. 30. 6392 4529



